

# OMNI 2" XS

Dodecahedral sound source



## Table of contents

|                                    |   |
|------------------------------------|---|
| <b>Tested Source</b> .....         | 3 |
| <b>Measuring environment</b> ..... | 4 |
| <b>Measuring equipment</b> .....   | 6 |
| <b>Results</b> .....               | 7 |
| Sound power .....                  | 7 |
| Sound pressure .....               | 8 |
| Directivity .....                  | 9 |

---

This paper shows the results of the measurements done to assess the compliance of the sound sources with the requirements stated in **ISO Standards 3744 and 3382** about sound power and directivity of sound sources.

The entire measurement was conducted following the guidelines provided by the International Standard Organisation about this kind of tests, in particular the procedure is compliant with **ISO Standard 17025**.

## Tested Source

| Model                                   | Dimensions (mm) | Weight (Kg) | Numeber of speakers |
|-----------------------------------------|-----------------|-------------|---------------------|
| OMNI 2" XS omnidirectional sound source | 200 x 200 x 300 | 2.5         | 12                  |

The sound source was fed with pink noise using an AMG mini digital amplifier.

During the measurement the sound source was installed on a rotating device (MB01) free to move on its central axis for 360° (see Fig. 1).





Fig. 1 Photos of measured source and measurement conditions

## Measuring environment

| Type                  | Temperature                 | Humidity       | Pressure                 |
|-----------------------|-----------------------------|----------------|--------------------------|
| Hemi-anechoic chamber | $23 \pm 1^{\circ} \text{C}$ | $30 \pm 15 \%$ | $994 \pm 10 \text{ hPa}$ |

In *Figure 2* is reported a simple drawing of the anechoic chamber used for this measurement. The height of the chamber is 2.63 m.




Fig. 2 Mic placement – Mic 1 is for sound power measurement, while Mic 2 is for sound pressure one. Distances in mm




Fig. 3 Representation of measurement procedure as indicated in ISO 3744

The chosen procedure was the one of a high machine with a narrow base due to the assembly of the sound source (see *Source Tested for a reference*).

The next tables show the values of L1, L2, L3 and D for this speaker and, hence, the values of A, B, C and S.

| L1 (m) | L2 (m) | L3 (m) | D (m) |
|--------|--------|--------|-------|
| 0.20   | 0.20   | 1.70   | 0.5   |

| A (m) | B (m) | C (m) | S (m <sup>2</sup> ) |
|-------|-------|-------|---------------------|
| 0.60  | 0.60  | 2.20  | 12.00               |

K1 and K2 correction factor are negligible because of the environment of the measurement (hemi-anechoic chamber).

## Measuring equipment

| Device            | Model | Manufacturer | Serial number                     |
|-------------------|-------|--------------|-----------------------------------|
| Sound level meter | NL-52 | Rion         | 00342833                          |
| Microphone        | UC59  | Rion         | 12852                             |
| Preamplifier      | NH-25 | Rion         | 10461                             |
| Sound Calibrator  | NC-75 | Rion         | 34891821                          |
| Rotating device   | MB-01 | Ntek         | Ntek calibration<br>lab test tool |

The microphone used for the measurement was equipped with a windscreen.

To measure the sound source the Rotating device was used in order to “sample” the source every 5° as stated within the ISO Standard.

The microphone was left in the same position for the entire duration of the measurement.

The data acquired was, then, processed with the help of a dedicated software that, with a proper algorithm, led to the results indicated in *Results* section.

## Results

In this section are reported the results of the measurements about the sound power of the source and its directivity.

### Sound power




Fig. 4 Sound Power Level Spectrum - 1/3 oct

## Sound pressure

Lp linear: 107 dB




Fig. 5 Linear Sound Pressure Level – 1/3 octave

Lp: 104 dBA




Fig. 6 A Weighted Sound Pressure Level – 1/3 octave

## Directivity




Fig. 7 Directional response - 1/1 octave




Fig. 8 Directivity according to ISO 16283. Upper and lower curves are the ISO 16283 tolerances




Fig. 9 Directivity according to ISO 3382. Upper and lower curves are the ISO 3382 tolerances



#### COMPANY IDENTITY

Ntek is specialized in products and services for noise and vibration measurement and control, in all applicable acoustic fields.

The company has been able to improve in designing, developing and producing solutions that mix simplicity, portability and user-friendly products with excellent quality.

Ntek main goal is to supply a qualified service with a complete range of products delivered on time in order to guarantee its customers the chance to focus on their business.

To keep this promise we have strongly invested in innovation and production process with monitoring procedures certified by independent primary authority.

#### OUR VISION

We believe that acoustics is the basis of wellness and improvement of life quality. It's for this reason that we develop, innovate and produce equipment inspired to this philosophy.

#### HOW WE WORK

Ntek can ensure a high level of service, thanks to modern processes and new laboratories, completely equipped for different operations of design, production, measurement, check and control.

#### INTERNAL LOGISTICS AND STOCK

With its new operative location of 500 m<sup>2</sup> and its internal stock, Ntek guarantees available products in a short time according to customers' needs. Today we can handle an order in 48 hours compared with a standard delivery of 45/60 days.

The new location is structured to be flexible with logistics activities and in answering efficiently to productive needs of our customers.

#### SUSTAINABILITY

Green company, environmentally friendly, aimed to a continuous improvement of quality and safety in industrial processes.

#### Ntek S.r.l.

Via Giuseppe Gabrielli, 18  
10077 San Maurizio Canavese (TO)  
ITALY  
[www.ntek.it](http://www.ntek.it)  
[info@ntek.it](mailto:info@ntek.it)  
+39 011 40 53 600

